

The one you trust in tonometry.

Tono-Pen®

Handheld Tonometers



Reichert
TECHNOLOGIES

AMETEK

reichert.com

Tono-Pen AVIA®



Tono-Pen®[®], for the clinician passionate about patient IOP.

Tono-Pen® has been the trusted choice of doctors and technicians for more than 30 years. Supported by hundreds of publications, Tono-Pen provides fast, accurate, and reliable IOP measurements that are less sensitive to corneal centration, and can be taken in any position, including patients in beds or wheelchairs. Tono-Pen is easy-to-use and requires minimal training.

The advanced **Tono-Pen AVIA®** builds on all the features that make the classic **Tono-Pen® XL** the most widely used handheld tonometer.



Tono-Pen® XL



Tono-Pen AVIA®

Tono-Pen® XL

Accurate IOP
Measurements
Correlating Strongly
with Goldmann

•

•

Handheld and Lightweight

•

•

One Button Operation

•

•

Uses Genuine
Ocu-Film® + Tip Covers

•

•

Quick-Tap™ Measurement Mode

•

No Calibration Required

•

Large Dual Displays

•

Modern Ergonomic
Design

•

Long-life Battery

•

On-screen
Battery Indicator

•

Soft-touch Grips

•

Tono-Pen AVIA[®]

Tono-Pen AVIA handheld tonometer requires no calibration and is always ready-to-use. An award winning ergonomic design, longer battery life, enhanced IOP averaging technique, now available in two measurement modes, making it the most advanced Tono-Pen yet.

No Calibration Required.

Routine calibration of Tono-Pen AVIA is not required. Spend less time worrying about your instruments and more time with your patients.



Award Winning Ergonomic Design.

With its award-winning, ergonomic design and soft-touch grips, the lightweight Tono-Pen AVIA fits comfortably in any operator's hand, ensuring consistent measurement technique among users.



Simple One Button Operation.

To take a measurement, simply press the button once. When the light turns to green, Tono-Pen AVIA is ready to use. Gently tap the anesthetized cornea until a short beep sounds to alert the operator that the measurement is complete.





Less Sensitive to Corneal Centration.

Using micro-strain gauge technology, Tono-Pen AVIA is less sensitive to corneal centration than other tonometers and provides fast, accurate, and repeatable results with minimal operator bias.

Technician Friendly.

Simple one button operation, award winning ergonomics, less sensitivity to corneal centration, and statistical confidence indicator makes delegation of Tono-Pen AVIA to an eye care technician easy and worry-free. Minimal training is necessary to become proficient in obtaining reliable IOP measurements.



Gravity Independent.

Unlike most other tonometers, only Tono-Pen can be used in any position, making it easy to measure all patients, including those who may be in a wheelchair or bedridden.

Large Dual Sided Screens.

The IOP measurement is displayed on two large, easy-to-read, LCD screens making it suitable for both left and right handed users.



Now available with Quick-Tap™ Measurement Mode.



Select from one of two measurement modes; the traditional First Generation mode, which provides an IOP measurement typically in five taps, and now the Quick-Tap™ Second Generation Measurement Mode where you can obtain a reliable IOP measurement in as few as two taps. This is especially useful for patients that may be sensitive to the applanation.

Long-life Battery.

The convenient on-screen battery indicator ensures that Tono-Pen AVIA will always be ready for use. The removable Tono-Pen AVIA POWERCEL® battery pack is easily replaced, requiring no tools. Just squeeze and pull.




ADA Eligibility in the United States.

The purchase of Tono-Pen may qualify for ADA tax benefits. Refer to Americans with Disabilities Act, Title 26, Internal Revenue Code, Section 44.

Designed & assembled in USA.

Tono-Pen handheld tonometers are proudly designed, engineered, and assembled at our world headquarters in Buffalo, New York, USA.

DESIGNED & ASSEMBLED IN USA





Protect your Tono-Pen and your patients with genuine:

Ocu-Film[®] + Tip Covers

Disposable and affordable, single-use, sanitized Reichert Ocu-Film + Tip Covers protect your Tono-Pen, and are easy to apply. Using genuine brand Reichert Ocu-Film + Tip Covers guarantees you are using tip covers that are specifically engineered for proper performance of your Tono-Pen.

Using non-Reichert tip covers may cause Tono-Pen readings to be erratic or inaccurate, and may result in difficulty obtaining measurements. Non-Reichert tip covers may also contaminate the Tono-Pen transducer, potentially voiding the warranty, and resulting in the need for costly service to the instrument.

Reichert Ocu-Film + Tip Covers are FDA cleared and are blue in color to assure the user that the tip cover is the genuine brand approved for use with Tono-Pen AVIA and Tono-Pen XL Applanation Tonometers.



Tono-Pen® XL

The classic Tono-Pen XL is an easy-to-use, handheld tonometer providing IOP measurements that correlate strongly with Goldmann tonometry. Weighing only 2.1 ounces, Tono-Pen XL is lightweight and extremely portable, enabling operators to take fast and accurate IOP measurements anywhere, on any patient, and with minimal training. Clinicians worldwide have made the Tono-Pen XL tonometer a trusted part of their practice for more than three decades.

Specifications

Tono-Pen AVIA®

Dimensions	6.25 x 0.75 x 1.75 in. (16 x 2 x 4.4 cm)
Weight	2.4 oz (71 g)
Transducer	Micro Strain Gauge
Measurement Range	5 - 55 mmHg
Power Source	Tono-Pen AVIA POWERCEL® Battery Pack

Tono-Pen® XL

Dimensions	7.25 x 1 x 0.875 in. (18.42 x 2.54 x 2.22 cm)
Weight	2.1 oz (59.4 g)
Transducer	Micro Strain Gauge
Measurement Range	5 - 80 mmHg
Power Source	2 OCU-CEL™ XL Batteries

Catalog Numbers

230650	Tono-Pen AVIA Tonometer Starter Pack (Contains Tono-Pen AVIA, Carry Case, Instructional Manual, 1 box of 150 individually packaged Ocu-Film + Tip Covers, 1 Tono-Pen AVIA POWERCEL® Battery Pack)
230635	Tono-Pen XL Tonometer Starter Pack (Contains Tono-Pen XL, Carry Case, 1 box of Ocu-Film + Tip Covers, 1 Package of OCU-CEL™ XL Batteries, Manual)
230651	Ocu-Film + Tip Covers - Box of 150 (Sanitized in Individual Packaging)
230653	Ocu-Film + Tip Covers - Bulk Pack of 600
230577	Tono-Pen AVIA POWERCEL® Battery Pack
230570	OCU-CEL™ XL Batteries - 4 per package



Ocu-Film® + Tip Covers

Protect your Tono-Pen® and your patients.

www.tonopen.com



www.reichert.com

Tono-Pen® Tonometers are designed & assembled in USA.
Call Reichert at +1 716-686-4500, toll-free 1-888-849-8955,
or contact your Authorized Reichert Technologies Distributor.
© 2018 AMETEK, Inc. & Reichert, Inc. 230650-110-Rev-D